

Alfa Laval TJ40G Rotary Jet Head

TJ40G best in class in hygienic design

Application

The TJ40G rotary jet head provides 3D indexed impact cleaning over a defined period. It is automatic and represents a guaranteed means of achieving quality assurance in tank cleaning. Used in breweries, food and dairy processes and many other industries with a strict demand for hygienic tank cleaning. The device is suitable for processing, storage tanks and vessels between 50 and 500 m³ and industries that require a certain level of hygienic design.

The TJ40G is the best-in-class in hygienic design and tank cleaning performance.

Working principle

The flow of the cleaning fluid makes the nozzles perform a geared rotation around the vertical and horizontal axes. In the first cycle, the nozzles lay out a coarse pattern on the tank surface. The subsequent cycles continually bisects the coarser pattern into a denser pattern, until a full pattern is reached after 8 cycles.

Unique features

Self cleaning: The TJ40G is designed with numerous of features that ensure self cleaning of the machine, such as directional flow from small jest in the hub that cleans the exterior of the machine.

Low pressure drop: A low pressure loss over the machine provides increased cleaning efficiency compared with other tank cleaning machine running at same inlet pressure.

This result in lower cleaning cost as the unit can run at lower pressure/flow compared to other tank cleaning machines.

Burst cleaning: The special nozzle design on the TJ40G Burst is designed for fast chemical wetting of the tank, this way of cleaning reduces time, water and chemical. For more information see the datasheet TJ40G Burst

Available versions

- TJ40G
- TJ40G Burst cleaning
- TJ40G-HD for Heavy Duties


TECHNICAL DATA

Lubricant: Cleaning liquid

Standard Surface finish: Exterior surface finish Ra $0.5 \mu m$

Interior surface finish: Ra 0.8µm Max throw length (5 bar): 21.5 m Impact throw length (5 bar): . . . 10.5 m

Pressure



PHYSICAL DATA

Materials

AISI 316, SAF 2205, PFA, PEEK, EPDM

Temperature

Max. working temperature: 95°C Max. ambient temperature: 140°C

Weight: 6.3 kg

Options

Rotacheck - Electronic rotation sensor to verify coverage


Caution

Avoid hard and abrasive particles in the cleaning liquid, as this can cause increased wear and/or damage of internal mechanism. For low amount of particles in the cleaning media a 3mm strainer is recommend for both the TJ40G and TJ40G-HD For high amount of particles in the cleaning media a 0.1mm strainer (TJ40G) and 1mm (TJ40G-HD) is recommended Do not use for gas evacuation and air dispersion

Certificates

2.2, 3.1 material certificate and ATEX





				TJ40G-HD
	TJ40G	TJ40G Burst	TJ40G-HD	Burst
4xø6 fast	15.8	20.8	17.5	22.5
4x ø 6	15.8	20.8	17.5	22.5
4x ø 6,6	18.2	23.2	20.0	25.0
4x ø 7,3	20.9	25.9	22.5	27.5
4x ø 8,1	24.9	29.9	26.5	31.5
4x ø 9	29.1	34.1	31.0	36.0
4x ø 10	33.8	38.8	35.5	40.5
4x ø 11	39.0	44.0	41.0	46.0
2xø10	19.2	21.7	20.3	22.8

24.9


23.4


25.9

Dimensions (mm)

22.4


2x**ø**11






Throw length measured according to tech. specification 93P003

Cleaning time for complete pattern (= 8 cycles)



Burst cleaning version has a 20-25% faster complete pattern

Cleaning Pattern





First cycle

Full pattern

The above drawings show the cleaning pattern achieved on a cylindrical horizontal vessel. The difference between the first cycle and the full pattern represents the number of additional cycles available to increase the density of the cleaning.

Standard Design

The choice of nozzle diameters can optimize jet impact length and flow rate at the desired pressure.

A Hygienic welding, female or male adaptor is available for following connections : Welding adaptors : 2" / 2'' dairy pipes, 1'/2" / 2" ISO pipe, DN40 / DN50 / DN65


Female adaptors: 1½" BSP, 1½" / 2" NPT


Male adaptors : 1½" / 2" BSP, 1½" / 2" NPT

The hygienic design of the TJ40G makes it the best in class for hygienic design. As standard documentation, it can be supplied with a "Declaration of Conformity" for material specification.


TRAX simulation tool

Wetting Intensity





D4.6m H5.5m, Toftejorg TJ40G, $4 \times \emptyset 7.3$ mm, Time = 2 min., Water consumption = 700 I



D4.6m H5.5m, Toftejorg TJ40G, $4 \times \text{ }$ 97.3 mm, Time = 16 min., Water consumption = 5600 I

Alfa Laval reserves the right to change specifications without prior notification.

How to contact Alfa Laval